

FiberKleen™

FiberOptic Cleaning System

FiberKleen™ Dry Towels meet Telcordia Specification

- Ultra-clean microfiber fabric material
- Hard plastic box prevents towel contamination
- Cleaning pad/surface on top of box
- 175 wipes per roll; refills available
- Durable towel has a smooth surface
- Non-linting, non-fraying
- High absorbency
- Engineered for optimum particle entrapment
- Best when used with **QuickKleen™** and **AquaKleen™** cleaner.



FiberKleen™ Holder

- Holds towel for ten wipes per towel
- Provides 1,750 cleanings per roll
- May be used wet or dry
- Swabs also available



www.polywater.com

American
Polywater[®]
Corporation

FiberKleen™ Accessories are best used with the combination wet - dry cleaning procedure recommended in Telcordia GR-2923-CORE. Microfiber towels (DT-D175) and holder (FC-HOLDER), available from American Polywater® Corporation work well with this method. Several drops or a light spray of AquaKleen™ or QuicKleen™ cleaner is placed on the towel. Preferred cleaning motion is a straight line motion, drawing the

endface through the wetted portion of the towel, and then through a clean portion of a second dry towel. Use of the FC-HOLDER optimizes the cleaning process. Swabs may be dampened on the wetted portion of the towel in order to clean the bulkhead or equipment.

FiberKleen™ Dry Towels offer high absorbency and are made from non-linting, non-fraying, ultra-clean material. This specialty, microfiber fabric is engineered for optimum particle entrapment. The durable towel has a smooth surface for easy cleaning. It meets Telcordia Specification.



CAT #	PACKAGE DESCRIPTION	CASE QTY
DT-D175	175-Towel FiberKleen™ Dispenser w/Cleaning Pad	12
FC-HOLDER	Dual towel holder with 20 slots for precision wet-dry cleaning	6
DT-D175H	FiberKleen™ Microfiber Towel Kit: 1 DT-D175 1 FC-HOLDER	6
SWB-250F100	2.5 mm FiberKleen™ foam swab (100 pack)	5
SWB-125F10	1.25 mm FiberKleen™ foam swab (10 pack)	5
SWB-C100	FiberKleen™ cotton swab (100 pack)	5
SWB-V100	V Groove FiberKleen™ foam swab (100 pack)	5
SWB-M100	Mirror FiberKleen™ foam swab (100 pack)	5

CAT #	PACKAGE DESCRIPTION	CASE QTY
AQ-2DR	AquaKleen™ Type AQ™ 2-Oz Dropper Bottle	12
AQ-2LP	AquaKleen™ Type AQ™ 2-Oz Finger Sprayer	12
AQ-KIT2	AquaKleen™ Kit with Finger Sprayer 2 AQ-2LP 1 DT-D175 1 FC-HOLDER 1 SWB-250F100	each
AQ-KIT3	AquaKleen™ Kit with Dropper Bottles 2 AQ-2DR 1 DT-D175 1 FC-HOLDER 1 SWB-250F100	each
AQ-WETDRY1	AquaKleen™ Wet/Dry Wipe Tandem Pack™	each
QC-2LP	2-oz QuicKleen™ Fiber Cleaner Finger Sprayer	12
QC-KIT2	QuicKleen™ Fiber Cleaner Kit: 2 QC-2LP 1 DT-D175 1 FC-HOLDER 1 SWB-250F100 1 DT-D175	each

Important Notice: The statements here are made in good faith based on tests and observations we believe to be reliable. However, the completeness and accuracy of the information is not guaranteed. Before using, the end-user should conduct whatever evaluations are necessary to determine that the product is suitable for the intended use.

American Polywater expressly disclaims any implied warranties and conditions of merchantability and fitness for a particular purpose. American Polywater's only obligation shall be to replace such quantity of the product proven to be defective. Except for the replacement remedy, American Polywater shall not be liable for any loss, injury, or direct, indirect, or consequential damages resulting from product's use, regardless of the legal theory asserted.



American Polywater Corporation

1-800-328-9384
1-651-430-2270
fax 1-651-430-3634
custserv@polywater.com (e-mail)